


# SF301A, SF302 Call Cords Specification Sheet



### ARCHITECTS' AND ENGINEERS' SPECIFICATION

Call cords shall be TekTone<sup>®</sup> SF301A, SF302, or approved equal. Model SF301A shall provide one molded push button. Model SF302 shall provide a "Y" type cord with two molded push buttons. The call cords shall be waterproof and shall be suitable for use in oxygen environments.

The momentary-contact push button cordsets shall be encased in a molded, shock-proof plastic shell. They shall be connected to a 7' (2.13 m) long polyvinyl covered cord with an integrally molded right-angle plug.

The SF301A and SF302 shall be UL® 1069 Listed.

# FEATURES

The TekTone<sup>®</sup> SF301A (single) or SF302 (double) call cords are for use with the Tek-CARE<sup>®</sup> NC110N, NC150N, NC200N and NC300<sup>™</sup>II Nurse Call Systems, and the Tek-CARE<sup>®</sup>500 Wireless Emergency Call System, where <sup>1</sup>/<sub>4</sub>" phono jacks are used. Ten-foot cords are also available as SF301A/10 and SF302/10. The SF301A and SF302 are oxygen safe call cords certified safe for use by all patients receiving oxygen therapy. These waterproof and impact resistant call cords have completely sealed push buttons.

- UL® 1069 Listed
- Oxygen safe
- Impact resistant and waterproof
- Small, lightweight pendant fits comfortably in hand
- Bed clips included

### SPECIFICATIONS

Connection:	<sup>1</sup> /4" (6.35 mm) plug-in phono jack
Construction:	SPST1-A switch
	Integral brass, fine silver contacts
	1 AMP, 115 watt maximum, AC
Dimensions:	7' (2.13 m) long polyvinyl covered cord

# **REQUIRED COMPONENTS**

Tek-CARE®500 Wireless Emergency Call System with SF530 Room Station

or

Tek-CARE® NC300<sup>™</sup>II Nurse Call System with SF380A Patient Stations

or

 $Tek\text{-}CARE^{\circledast} NC200N \, or \, NC150N \, Nurse \, Call \, Systems \\ with \, IR151B \, or \, IR152B \, Patient \, Stations$ 

or

Tek-CARE® NC110N Nurse Call System with SF100C or SF102 Patient Stations

### www.tektone.com

277 Industrial Park Road • Franklin, NC 28734 • tektone@tektone.net Phone: (828) 524-9967 • Fax: (828) 524-9968 • Tech Support: Choose option 2 • Sales: Choose option 3 **TekTone®'s quality system is registered by UL® to the ISO 9001 standard. (Reference #10001510.)**